

# ALPA Groundglass Mask for Stitching

Print in 100 % on overhead projector transparency and cut along the outer frame. Use on top of the groundglass. If a Fresnel screen is used do **not** put it between groundglass and screen.

The mask shows the virtual sensor (shifted) with the maximum shift of the ALPA 12 MAX and/or a minimal overlap of one mm sensor size. The theoretical overlap is indicated with dashed lines.

The mask for the 4x stitch shows a little bit less than the effective stitched area as the mask height is limited to 71 mm.

Version 40x54 (for sensors with dimensions of 40x54 mm)

ALPA of Switzerland, July 2009

